

**RECARO – the car seat that meets the highest safety standards; for very small children**

**9 – 22 kg**  
**19.8 – 48.5 lb**  
**body weight**



**RECARO** & **Thomashilfen**  
**A strong partnership**

**Car seat RECARO Expert plus Reha**

# Car seat **RECARO Expert plus Reha**

- Quick fitting system
- ECE group I, approved acc. to current test standard ECE R 44/04
- 5-point safety belt with practical central adjuster
- Integrated seat tilt-in-space to rest and sleep position
- Pad system as standard
- Carry handle for easy transport

## Functions



Patented quick fitting system using vehicle's 3-point belt



Integrated 5-point safety belt



Adjustment to rest position where only seat surface and back need to be moved

## Accessories




Footrest with footrest adapter



Table



Seat wedge, below



Car seat protection mat with back

| Measurements & weights                | RECARO Expert plus Reha   |
|---------------------------------------|---|
| <b>Seat depth</b>                     | 29 cm / 11.4" (26 cm / 10.2" with seat pads)  |
| <b>Seat width</b>                     | front 29 cm / 11.4" (22 cm / 8.7" with seat pads)<br>rear 28 cm / 11" (22 cm / 8.7" with seat pads) |
| <b>Back height</b>                    | 55 / 21.7"  |
| <b>Overall dimensions (w x h x d)</b> | 43 x 67 x 56 cm / 16.9 x 26.4 x 22"   |
| <b>Max. weight capacity</b>           | 9 – 22 kg / 19.8 – 48.5 lb  |
| <b>Weight of seat</b>                 | approx. 11 kg / 24.3 lb   |

| Products & accessories   | item code  |
|--|------------|
| <b>RECARO Expert plus Reha</b>   | <b>860</b> |
| Footrest, short* (depth: 12 cm / 4.7") (tiltable and adjustable in angle)  | 806        |
| Seat wedge, below  | 810        |
| Car seat protection mat  | 813        |
| Car seat protection mat incl. back   | 814        |
| Table  | 865        |
| Footrest adapter*  | 866        |
| Fabric Bellini, light grey (per running metre) (for custom-made solutions) | E89011     |
| Fabric Bellini, dark grey (per running metre) (for custom-made solutions)  | E89012     |

\* The adapter must be ordered to use the footrest